



Wedge block "Herkules", highest support height: 190mm



Order data

Order number	374900 190
GTIN	4020772072797
Item class	35A

Description

Version:

Very rigid design; spheroidal graphite cast iron and hardened steel. **The ground wedge surfaces provide for precision and even height adjustment** with an accuracy better than 0.1mm. Either the knurled screw or a hexagon socket wrench can be used for height adjustment. The double action results in a long stroke and precise vertical movement without lateral displacement.

Application:

Particularly for working with heavy cast or forged parts on large machine tools after marking-out.

Supplied with:

Interchangeable ball jack pad No. 375000.

Note:

Flat component support face with centring hole \varnothing 12 mm for jack pads No. 375000 – 375030.

Technical description

highest support height	190 mm
Load capacity	250 kN
Height adjustment per spindle rotation	2.02 mm

lowest support height	170 mm
Footprint width	145 mm
Footprint length	175 mm
Type	6460
Type of product	Wedge