

PLANOLITH**Universal precision comparator stand Granite, Table length: 150mm****Order data**

Order number	442534 150
GTIN	2050002047037
Item class	46H

Description**Version:**

Stand table precision diamond lapped. Extremely rigid and solid structure. Natural granite table of finest quality and hardness.

Precision comparator stand with universal measuring arm. 3-point clamping for high stiffness.

Dial indicator holder with fine adjustment, for shank \varnothing 6 mm, 8 mm, 3/8 inch and lever dial indicators with dovetailed clamping slides.

Flatness $\leq 2 \mu\text{m}$.

Technical description

Measuring face width	100 mm
Throat	120 mm
Column \varnothing	16 mm
Weight	2.8 kg
Measuring face length	100 mm
Table length	150 mm

Table width	100 mm
Cross arm Ø	14 mm
Connection thread	M10
Maximum measuring height	210 mm
Standard	DIN 876
Calibration	D1
Type of product	Comparator stand

Services

CalibrationComparator stand maximum table size 400X400 mm	024580 400X400
--	----------------