

**Heavy screw jack, highest support height: 300mm****Order data**

Order number	374400 300
GTIN	4020772072636
Item class	35A

Description**Version:**

- Spindle quenched and tempered steel; body quenched and tempered steel, painted.
- Spindle with trapezoidal thread.

Note:

With centring hole \varnothing 12 mm for jack pads No. 375000 - 375030.

Technical description

Foot length	220 mm
Foot width	190 mm
Slot width	26 mm
lowest support height	200 mm
Centre slot spacing	150 mm
Load capacity	80 kN
highest support height	300 mm

Head size AF	65 mm
Type	6435S
Type of product	Screw jack