



## Flat clamp, Slot width a: 22mm



### Order data

Order number	375115 22
GTIN	4020772374198
Item class	35A

### Description

#### Version:

Low design, position the flat clamp on the workpiece. Then tighten the securing screws for the machine table. The workpiece is clamped by turning the clamping screw.

#### Application:

**For lateral clamping of especially thin components**, in order to perform complete machining operations without interference contours. Can be used both horizontally and vertically.

#### Material:

Hardened steel, burnished finish.

### Technical description

Intermediate height $H_1$	22 mm
Minimum height $h_1$	22 mm
Clamping force $F_2$ vertical	18 kN
Thread G	M20
Clamping force $F_1$ horizontal	36 kN
Maximum height $h_2$	36 mm
Slot width a	22 mm
Length L	152 mm
Width B	62 mm

Type	6496
Type of product	Side clamps