

PLANOLITH**Universal precision comparator stand Granite, Table length: 260mm****Order data**

Order number	442534 260
GTIN	2050002047044
Item class	46H

Description**Version:**

Stand table precision diamond lapped. Extremely rigid and solid structure. Natural granite table of finest quality and hardness.

Precision comparator stand with universal measuring arm. 3-point clamping for high stiffness.

Dial indicator holder with fine adjustment, for shank \varnothing 6 mm, 8 mm, 3/8 inch and lever dial indicators with dovetailed clamping slides.

Flatness $\leq 2 \mu\text{m}$.

Technical description

Measuring face length	200 mm
Table width	140 mm
Throat	210 mm
Measuring face width	140 mm
Cross arm \varnothing	16 mm
Weight	7 kg

Maximum measuring height	260 mm
Connection thread	M10
Column Ø	18 mm
Table length	260 mm
Standard	DIN 876
Calibration	D1
Type of product	Comparator stand

Services

CalibrationComparator stand maximum table size 400X400 mm	024580 400X400
--	----------------