



Screw jack with steel base, highest support height: 300mm



Order data

Order number	373500 300
GTIN	4020772072445
Item class	35A

Description

Version:

Quenched and tempered steel, painted.
Self-locking trapezoidal thread spindle with end stop.

Note:

From size 52 with centring hole \varnothing 12 mm for jack pads No. 375000 – 375030.

Technical description

lowest support height	190 mm
Load capacity	350 kN
highest support height	300 mm
Head \varnothing	80 mm
for clamp with slot width	20 - 40 mm
Lower part \varnothing	100 mm
Type	6400

Type of product

Screw jack