

**Heavy screw jack, highest support height: 750mm****Order data**

Order number	374400 750
GTIN	4020772072650
Item class	35A

Description**Version:**

- Spindle quenched and tempered steel; body quenched and tempered steel, painted.
- Spindle with trapezoidal thread.

Note:

With centring hole \varnothing 12 mm for jack pads No. 375000 - 375030.

Technical description

Foot width	190 mm
Foot length	220 mm
Slot width	26 mm
Head size AF	65 mm
lowest support height	430 mm
Load capacity	50 kN
Centre slot spacing	150 mm

highest support height	750 mm
Type	6435S
Type of product	Screw jack