



Flat clamp, Slot width a: 28mm



Order data

Order number	375115 28
GTIN	4020772374211
Item class	35A

Description

Version:

Low design, position the flat clamp on the workpiece. Then tighten the securing screws for the machine table. The workpiece is clamped by turning the clamping screw.

Application:

For lateral clamping of especially thin components, in order to perform complete machining operations without interference contours. Can be used both horizontally and vertically.

Material:

Hardened steel, burnished finish.

Technical description

Clamping force F_2 vertical	18 kN
Clamping force F_1 horizontal	36 kN
Slot width a	28 mm
Maximum height h_2	36 mm
Minimum height h_1	22 mm
Intermediate height H_1	22 mm
Thread G	M20
Length L	152 mm
Width B	62 mm

Type	6496
Type of product	Side clamps