

Mitutoyo**Precision vernier height gauge, Marking height: 200mm****Order data**

Order number	443500 200
GTIN	4946368091303
Item class	44A

Description**Version:**

Sturdy base with ground base, **scale hardened and ground.**

All reading parts are anti-glare satin chrome-plated. Sharp jet black scales. With fine adjustment. Slightly raised edges to the scale prevent the slide from damaging it. Reading zero and marking scribe are adjusted with reference to the bottom of the base (marking out from "0"). Drawing dimensions can therefore be transferred directly without the risk of calculation errors.

The scribe is **carbide tipped.**

Technical description

Column cross section	20×6 mm
Marking height	200 mm
Base width	65 mm
Base length	100 mm
Calibration	E1
Vernier	1/50 mm

Error limit	0.03 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum measuring range 300 mm	024630 300
DAkkS calibrationHeight gauge / height scriber maximum measuring range 300 mm	024640 300

Accessories

Spare scriber, carbide tipped for marking heights 200 mm	443510 200
--	------------