

**Vernier depth gauge, Measuring range: 1000mm****Order data**

Order number	418000 1000
GTIN	4045197203625
Item class	41Z

Description**Version:**

Measuring beam and vernier with clearly engraved scales. Precision ground contact faces. Vernier satin chrome-plated.

Supplied with:

From size 500 in a case.

Technical description

Measuring range	0 - 1000 mm
Measuring tip a	10 mm
Vernier length	39 mm
Cross-section measuring beam	20×5 mm
Measuring tip b	13 mm
Bridge length	250 mm
Graduation	1/20 mm
Packaging	sturdy box
Measurement deviation E MPE	± 0.15 mm
Standard	ISO 13385
Measurement technology	analogue

Material	Stainless steel, INOX
all parts	hardened
Calibration	A1
Type of product	Depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000