



Digital depth gauge TWIN CAL IP 67, Measuring range: 250 mm



Order data

| | |
|--------------|---------------|
| Order number | 418695 250 |
| GTIN | 7630041106497 |
| Item class | 45A |

Description

Version:

Large digital display 11 mm, IP67 protection, "Soft touch" casing, 12,000hours service life, automatic standby after 10min. and automatic shutdown after 2h, TLC-TWIN interface, offset measuring face 4 mm wide.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

General purpose use for depth measurement, holes, offsets, width and spacing measurements.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

Packaging: sturdy box

Interface: USB interface

Interface: Digimatic interface

Interface: TESA Link Connector TLC

IP Index of Protection: IP 67

Calibration: A1

Reversible reading: 0.01 mm

Reversible reading: 0.0005 inch

Error limit: 0.03 mm

Bridge length: 100 mm

Cross-section measuring beam: 15x4 mm

Technical description

| | |
|---|-----------------------------|
| Digit height LCD display | 11 mm |
| Bridge length | 100 mm |
| Measuring range | 0 - 250 mm |
| Calibration | A1 |
| Cross-section measuring beam | 15×4 mm |
| Interface | USB interface |
| Interface | Digimatic interface |
| Interface | TESA Link Connector TLC |
| Working time | 12000 h |
| Reversible reading | 0.0005 inch |
| Reversible reading | 0.01 mm |
| Error limit | 0.03 mm |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| Number of batteries contained | 1 |
| IP Index of Protection | IP 67 |
| Power supply | Battery-powered |
| Standard | Manufacturer's standard |
| Reversible reading | mm / inch |
| Measurement technology | digital |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Packaging | sturdy box |
| Type of product | DEPTH GAGE, STAINLESS STEEL |

Services

| | |
|--|------------|
| Calibration Calipers / depth gauges maximum measuring range 300 mm | 011030 300 |
| Labelling laser-etched Type | 018940 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm | 011050 300 |

| | |
|--|------------|
| Calibration Calipers / depth gauges maximum measuring range 300 mm | 021000 300 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm | 021010 300 |

Accessories

| | |
|---|----------------|
| Software Data-Direct | 498925 |
| Transmitter Type S121 | 498966 S121 |
| Data cable TLC, 2 m Type USB | 498918 USB |
| Radio receiver TWIN Station Type STATION | 498917 STATION |
| Stat-Express software | 498926 |
| Multi-receiver / USB keyboard interface Type | 498975 |
| Radio transmitter TLC-TWIN Type SENDER | 498916 SENDER |
| Data cable TLC, 2 m Type D | 498918 D |
| Receiver / USB keyboard interface Type | 498965 |
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |