



Vernier depth gauge, Measuring range: 300mm



Order data

Order number	418300 300
GTIN	4045197203656
Item class	41Z

Description

Version:

Measuring beam and vernier satin chrome-plated. Vernier adjustable. High-contrast scale.
Measuring and contact faces precision lapped. Wider bridging widths achievable by using extension base(see No. 418744).

Optional extras:

Additional extension base No. 418744 (180 – 320 mm).

Technical description

Cross-section measuring beam	11×4 mm
Vernier length	39 mm
Measuring range	0 - 300 mm
Graduation	1/20 mm
Bridge length	100 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.08 mm
Standard	ISO 13385
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened

Calibration	A1
Type of product	Depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Single extension base Bridge length 260 mm	418744 260
Single extension base Bridge length 320 mm	418744 320
Single extension base Bridge length 180 mm	418744 180