



Digital groove depth gauge, Measuring range: 950mm



Order data

Order number	418755 950
GTIN	4045197640901
Item class	42A

Description

Version:

Digital depth gauge for measuring slots, grooves, recesses, offsets and holes. Weight-saving construction of aluminium profile reinforced with steel, with anodised surfaces. Optimum guidance and sliding characteristics due to internal double Vee guides. Various different measuring tips (M2.5) can be screwed into the measuring rod.

Aluminium profile with steel reinforcement and anodised surface. Double Vee guides.

Exchangeable measuring tips (M2.5).

Application:

Measuring cut-outs, grooves, holes and offsets.

Supplied with:

Measuring tip with steel ball, disc insert No. 434900 size 11, measurement heads 150 mm and 350 mm, battery No. 081560 size LR44.

Note:

Measurement heads 550 mm, 750 mm and 900 mm on request.

Technical description

Measuring range	0 - 950 mm
Cross-section measuring beam	23.5 × 9 mm
Calibration	A1
Disc anvil Ø	20 mm
Measuring rod Ø	6 mm
Reversible reading	mm / inch

Error limit	0.06 mm
Article no of the battery / rechargeable battery fitted	081560 LR44
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Type of product	Groove depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000

Accessories

Button cell / special battery Battery type LR44	081560 LR44
---	-------------