



Digital universal depth gauge, Measuring range: 300mm



Order data

Order number	418770 300
GTIN	2050001670854
Item class	46P

Description

Version:

Flexible universal depth gauges with exchangeable measuring tips. For measuring cut-outs, grooves, recesses, shoulders etc. Precision lapped measuring faces.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Depth gauge, double hook measuring tip No. 418772 size A, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948.

Measuring tips No. 418772.

Measurement head No. 418774.

Technical description

Interface	RS232 interface
Interface	USB interface
Calibration	A2
Bridge length	150 mm
Measuring range	0 - 300 mm
Cross-section measuring beam	12×4 mm
Reversible reading	0.0005 in

Reversible reading	0.01 mm
Error limit	0.03 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

DAkkS calibration Vernier hook depth gauge maximum measuring range 300 mm	021230 300
Calibration Vernier hook depth gauge maximum measuring range 300 mm	021220 300

Accessories

Receiver / USB keyboard interface Type	498965
Measurement head for depth gauge No. 418770 Bridge length 400 mm	418774 400
Measuring tip for depth gauge No. 418770 Type D	418772 D
Measuring tip for depth gauge No. 418770 Type B	418772 B
Measurement head for depth gauge No. 418770 Bridge length 600 mm	418774 600
Multi-receiver / USB keyboard interface Type	498975
Measuring tip for depth gauge No. 418770 Type A	418772 A

Connection cable Duplex Type USB2	498950 USB2
Measuring tip for depth gauge No. 418770 Type C	418772 C
Button cell / special battery Battery type CR2032	081560 CR2032
Measurement head for depth gauge No. 418770 Bridge length 500 mm	418774 500
Connection cable Duplex Type 2	498950 2