



Small comparator stand, Type: 50



Order data

Order number	442930 50
GTIN	4030234000008
Item class	46K

Description

Version:

Strong cast iron base with rigid column and sturdy indicator holder. The table is hardened, ground, and lapped. Indicator holder \varnothing 8 mm.

Table face with dust grooves. Sturdy version without fine adjustment.

Flatness $\leq 5 \mu\text{m}$.

Calibration: D1

Throat: 49 mm

Maximum measuring height: 100 mm

Column \varnothing : 22 mm

Table \varnothing : 50 mm

Overall height: 200 mm

Weight: 2.3 kg

Technical description

Column \varnothing	22 mm
Throat	49 mm
Weight	2.3 kg

Maximum measuring height	100 mm
Overall height	200 mm
Table Ø	50 mm
Standard	DIN 876/0
Calibration	D1
Type of product	Small comparator stand

Services

Calibration Comparator stand maximum table size 400X400 mm	016220 400X400
Labelling laser-etched Type	018940
Calibration Comparator stand maximum table size 400X400 mm	024580 400X400