



Digital universal depth gauge, Measuring range: 400mm



Order data

| | |
|--------------|---------------|
| Order number | 418770 400 |
| GTIN | 2050001670861 |
| Item class | 46P |

Description

Version:

Flexible universal depth gauges with exchangeable measuring tips. For measuring cut-outs, grooves, recesses, shoulders etc. Precision lapped measuring faces.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Depth gauge, double hook measuring tip No. 418772 size A, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948.

Measuring tips No. 418772.

Measurement head No. 418774.

Technical description

| | |
|------------------------------|-----------------|
| Bridge length | 150 mm |
| Calibration | A2 |
| Measuring range | 0 - 400 mm |
| Interface | RS232 interface |
| Interface | USB interface |
| Cross-section measuring beam | 12×4 mm |
| Reversible reading | 0.0005 in |

| | |
|---------------------------------------------------------|-------------------------|
| Reversible reading | 0.01 mm |
| Error limit | 0.03 mm |
| Number of batteries contained | 1 |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| IP Index of Protection | IP 67 |
| Power supply | Battery-powered |
| Standard | Manufacturer's standard |
| Reversible reading | mm / inch |
| Measurement technology | digital |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Packaging | sturdy box |
| Type of product | Depth gauge |

Services

| | |
|---------------------------------------------------------------------------|------------|
| Calibration Vernier hook depth gauge maximum measuring range 500 mm | 021220 500 |
| DAkkS calibration Vernier hook depth gauge maximum measuring range 500 mm | 021230 500 |

Accessories

| | |
|------------------------------------------------------------------|---------------|
| Measurement head for depth gauge No. 418770 Bridge length 500 mm | 418774 500 |
| Connection cable Duplex Type 2 | 498950 2 |
| Measuring tip for depth gauge No. 418770 Type A | 418772 A |
| Measurement head for depth gauge No. 418770 Bridge length 600 mm | 418774 600 |
| Measuring tip for depth gauge No. 418770 Type C | 418772 C |
| Measuring tip for depth gauge No. 418770 Type B | 418772 B |
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |

| | |
|------------------------------------------------------------------|-------------|
| Measuring tip for depth gauge No. 418770 Type D | 418772 D |
| Measurement head for depth gauge No. 418770 Bridge length 400 mm | 418774 400 |
| Connection cable Duplex Type USB2 | 498950 USB2 |
| Receiver / USB keyboard interface Type | 498965 |
| Multi-receiver / USB keyboard interface Type | 498975 |