



## Digital depth gauge TWIN CAL IP 67, Measuring range: 350mm



### Order data

Order number	418697 350
GTIN	7630041106565
Item class	45A

### Description

#### Version:

Large digital display 11 mm, IP67 protection, "Soft touch" casing, 12,000hours service life, automatic standby after 10min. and automatic shutdown after 2h, TLC-TWIN interface, offset measuring face 4 mm wide.

**With 360° adjustable stop plate** for comprehensive measurement tasks.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Application:

General purpose use for depth measurement, holes, offsets, width and spacing measurements.

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Data cable No. 498918, radio No. 498921 size BT.

### Technical description

Calibration	A1
Bridge length	150 mm
Interface	USB interface
Interface	TESA Link Connector TLC
Interface	Digimatic interface

Reversible reading	0.01 mm
Cross-section measuring beam	15×4 mm
Reversible reading	0.0005 in
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.03 mm
Standard	ISO 13385
Reversible reading	mm / inch
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

## Services

CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500
DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500

## Accessories

Receiver / USB keyboard interface Type	498965
Button cell / special battery Battery type CR2032	081560 CR2032
Data cable TLC, 2 m Type USB	498918 USB
Data cable TLC, 2 m Type D	498918 D
Multi-receiver / USB keyboard interface Type	498975