



## Digital depth gauge with data output, Measuring range: 150 mm

### Order data

Order number	418686 150
GTIN	4045197553744
Item class	41A

### Description

#### Version:

Easy-to-read, high-contrast LCD display with 8.5 mm high digits. Modern energy-efficient measurement system. The measuring faces are precision lapped. Measuring beam has a slender hardened measuring pin at the front, Ø 1.5 mm, 5 mm long.

#### Callout:

Extension base No. 41 8610

Measuring anvil No. 41 8630

#### Supplied with:

1 battery No. 081560 size CR2032

#### Optional extras:

Extension base 300 mm long No. 418610, measuring tip for caliper jaws No. 418630

Data cable No. 498940.

Norm: Manufacturer's standard

Reversible reading: mm / inch

Measured value saving: MAHR reference-lock system

Material: Stainless steel, INOX

all parts: hardened

Packaging: sturdy box

Interface: RS232 interface

Interface: USB interface

Interface: Digimatic interface

Calibration: A1

Reversible reading: 0.01 mm

Reversible reading: 0.0005 inch

Error limit: 0.03 mm

Bridge length: 100 mm

Cross-section measuring beam: 16x4 mm

### Technical description

Automatic stand-by circuit.	
Preset function	
Material	Stainless steel, INOX
all parts	hardened
IP Index of Protection	
Auto switch-off	
Norm	Manufacturer's standard
Measured value saving	MAHR reference-lock system
Packaging	sturdy box
Reversible reading	mm / inch
Measurement technology	digital
Measurement method of the measuring instrument	
Test certificate	
Type of product	DEPTH GAGE, STAINLESS STEEL