

Mitutoyo
Digital depth gauge with data output, Measuring range: 300 mm

Order data

| | |
|--------------|---------------|
| Order number | 418710 300 |
| GTIN | 4946368539379 |
| Item class | 44A |

Description
Version:

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Additional extension base No. 418744.

Data cables No. 497080 and 497100.

Packaging: Wallet

Interface: USB interface

Interface: Digimatic interface

Calibration: A1

Scale divisions: 0.01 mm

Error limit: 0.04 mm

Bridge length: 100 mm

Cross-section measuring beam: 16×3.5 mm

Technical description

| | |
|------------------------------|---------------------|
| Measuring range | 0 - 300 mm |
| Interface | USB interface |
| Interface | Digimatic interface |
| Cross-section measuring beam | 16×3.5 mm |
| Calibration | A1 |

| | |
|---|---------------------------------------|
| Scale divisions | 0.01 mm |
| Bridge length | 100 mm |
| Error limit | 0.04 mm |
| Number of batteries contained | 1 |
| Article no of the battery / rechargeable battery fitted | 081560 357 |
| Power supply | Battery-powered |
| Standard | Manufacturer's standard |
| Measured value saving | once-off setting of the zero position |
| Measurement technology | digital |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Packaging | Wallet |
| Type of product | DEPTH GAGE, STAINLESS STEEL |

Services

| | |
|--|------------|
| Calibration Calipers / depth gauges maximum measuring range 300 mm | 011030 300 |
| Labelling laser-etched Type | 018940 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm | 011050 300 |

Accessories

| | |
|--|-------------|
| Connecting cable with data switch Type D2 | 497100 D2 |
| Connecting cable with data switch Type USB2 | 497100 USB2 |
| Multi-receiver / USB keyboard interface Type | 498975 |
| Connecting cable Type D2 | 497080 D2 |
| Transmitter Type S1 | 498966 S1 |
| Button cell / special battery Battery type 357 | 081560 357 |
| Single extension base Bridge length 180 mm | 418744 180 |
| Connecting cable with data switch Type D1 | 497100 D1 |

| | |
|---|-------------|
| Connecting cable Type USB2 | 497080 USB2 |
| Receiver / USB keyboard interface Type | 498965 |
| Single extension base Bridge length 320 mm | 418744 320 |
| Single extension base Bridge length 260 mm | 418744 260 |
| Connecting cable Type D1 | 497080 D1 |
| Connecting cable with data switch Type D2 | 497085 D2 |
| Connecting cable with data switch Type D1 | 497085 D1 |
| Connecting cable with data switch Type USB2 | 497085 USB2 |