



## Digital universal depth gauge, Measuring range: 500mm



### Order data

Order number	418770 500
GTIN	2050001670878
Item class	46P

### Description

#### Version:

Flexible universal depth gauges with exchangeable measuring tips. For measuring cut-outs, grooves, recesses, shoulders etc. Precision lapped measuring faces.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Depth gauge, double hook measuring tip No. 418772 size A, 1 battery No. 081560 size CR2032.

#### Optional extras:

Data cable No. 498948.

Measuring tips No. 418772.

Measurement head No. 418774.

### Technical description

Cross-section measuring beam	12×4 mm
Interface	RS232 interface
Interface	USB interface
Bridge length	150 mm
Calibration	A2
Measuring range	0 - 500 mm
Reversible reading	0.0005 in

Reversible reading	0.01 mm
Error limit	0.03 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

## Services

DAkkS calibration Vernier hook depth gauge maximum measuring range 500 mm	021230 500
Calibration Vernier hook depth gauge maximum measuring range 500 mm	021220 500

## Accessories

Measuring tip for depth gauge No. 418770 Type D	418772 D
Measurement head for depth gauge No. 418770 Bridge length 400 mm	418774 400
Measuring tip for depth gauge No. 418770 Type C	418772 C
Measurement head for depth gauge No. 418770 Bridge length 500 mm	418774 500
Measuring tip for depth gauge No. 418770 Type B	418772 B
Connection cable Duplex Type 2	498950 2
Measuring tip for depth gauge No. 418770 Type A	418772 A

Measurement head for depth gauge No. 418770 Bridge length 600 mm	418774 600
Receiver / USB keyboard interface Type	498965
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type CR2032	081560 CR2032
Connection cable Duplex Type USB2	498950 USB2