



Vernier double hook depth gauge, Measuring range: 200mm



Order data

Order number	418520 200
GTIN	4045197203731
Item class	41Z

Description

Version:

Measuring beam and vernier satin chrome-plated, with cleanly engraved scales. Precision ground contact faces.

Application:

Universal for depth measurements, distances, recesses, and grooves - particularly in bores. Please note dimension "a".

Technical description

Bridge length	100 mm
Graduation	1/20 mm
Vernier length	39 mm
Cross-section measuring beam	10×3 mm
Measuring range	0 - 200 mm
Hook size a	23 mm
Packaging	Wallet
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Measurement technology	analogue
Material	Stainless steel, INOX

all parts	hardened
Calibration	A2
Type of product	Depth gauge

Services

Calibration Vernier hook depth gauge maximum measuring range 200 mm	021220 200
DAkkS calibration Vernier hook depth gauge maximum measuring range 200 mm	021230 200