



## Small comparator stand, Type: 115



### Order data

|              |               |
|--------------|---------------|
| Order number | 442930 115    |
| GTIN         | 4030234000374 |
| Item class   | 46K           |

### Description

#### Version:

Strong cast iron base with rigid column and sturdy indicator holder. The table is hardened, ground, and lapped. Indicator holder  $\varnothing$  8 mm.

Table face with dust grooves. Sturdy version without fine adjustment.

**Flatness  $\leq 5 \mu\text{m}$ .**

### Technical description

|                          |        |
|--------------------------|--------|
| Overall height           | 284 mm |
| Throat                   | 135 mm |
| Weight                   | 7.1 kg |
| Table width              | 98 mm  |
| Maximum measuring height | 150 mm |
| Table length             | 115 mm |
| Column $\varnothing$     | 28 mm  |

|                 |                  |
|-----------------|------------------|
| Cross arm Ø     | 20 mm            |
| Standard        | DIN 876/0        |
| Calibration     | D1               |
| Type of product | Comparator stand |

### Services

|  |                |
|--|----------------|
| CalibrationComparator stand maximum table size<br>400X400 mm | 024580 400X400 |
|--|----------------|