



Small comparator stand, Type: 115



Order data

Order number	442930 115
GTIN	4030234000374
Item class	46K

Description

Version:

Strong cast iron base with rigid column and sturdy indicator holder. The table is hardened, ground, and lapped. Indicator holder \varnothing 8 mm.

Table face with dust grooves. Sturdy version without fine adjustment.

Flatness $\leq 5 \mu\text{m}$.

Calibration: D1

Throat: 135 mm

Maximum measuring height: 150 mm

Column \varnothing : 28 mm

Cross arm \varnothing : 20 mm

Table length: 115 mm

Table width: 98 mm

Technical description

Overall height	284 mm
Throat	135 mm
Weight	7.1 kg

Table width	98 mm
Maximum measuring height	150 mm
Table length	115 mm
Column Ø	28 mm
Cross arm Ø	20 mm
Standard	DIN 876/0
Calibration	D1
Type of product	Small comparator stand

Services

Calibration Comparator stand maximum table size 400X400 mm	016220 400X400
Labelling laser-etched Type	018940
Calibration Comparator stand maximum table size 400X400 mm	024580 400X400