

Mitutoyo
Digital depth gauge with data output, Measuring range: 1000mm

Order data

Order number	418710 1000
GTIN	4946368377094
Item class	44A

Description
Version:

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Additional extension base No. 418744.

Data cables No. 497080 and 497100.

Technical description

Scale divisions	0.01 mm
Measuring range	0 - 1000 mm
Cross-section measuring beam	20×6 mm
Calibration	A1
Bridge length	250 mm
Interface	Digimatic interface
Interface	USB interface
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered

Measurement deviation E MPE	± 0.07 mm
Standard	ISO 13385
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	Wallet
Type of product	Depth gauge

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 1000 mm	021010 1000
Calibration Calipers / depth gauges maximum measuring range 1000 mm	021000 1000

Accessories

Single extension base Bridge length 180 mm	418744 180
Receiver / USB keyboard interface Type	498965
Connecting cable Type D2	497080 D2
Connecting cable with data switch Type D2	497100 D2
Connecting cable Type USB2	497080 USB2
Connecting cable with data switch Type D1	497100 D1
Connecting cable with data switch Type USB2	497085 USB2
Single extension base Bridge length 320 mm	418744 320
Connecting cable with data switch Type D2	497085 D2
Connecting cable with data switch Type USB2	497100 USB2
Connecting cable Type D1	497080 D1
Button cell / special battery Battery type 357	081560 357
Transmitter Type S1	498966 S1

Single extension base Bridge length 260 mm	418744 260
Connecting cablewith data switch Type D1	497085 D1
Multi-receiver / USB keyboard interface Type	498975