



Vernier height gauge with magnifying glass, Marking height: 300mm



Order data

Order number	443805 300
GTIN	4045197204714
Item class	42D

Description

Version:

Strong base with lapped standing surface. Reading 0.02 mm with fine adjustment. The scriber is **carbide tipped**. With adjustable measuring beam, magnifying glass and locking screw.

Technical description

Calibration	E1
Base width	90 mm
Marking height	300 mm
Base length	135 mm
Column cross section	28×9 mm
Vernier	1/50 mm
Error limit	0.06 mm
Standard	Manufacturer's standard

Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Height gauge and marking device

Services

DAkkS calibration Height gauge / height scriber maximum measuring range 300 mm	024640 300
Calibration Height gauge / height scriber maximum measuring range 300 mm	024630 300

Accessories

Spare scriber, carbide tipped Type R	443816 R
Spare scriber, carbide tipped Type E	443816 E