



Tee bolt (10.9. / 8.8.) complete, Type: 1412200



Order data

| | |
|--------------|----------------|
| Order number | 375300 1412200 |
| GTIN | 4020772080921 |
| Item class | 35A |

Description

Version:

T-bolt, forged and rolled thread.

Standard design, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

Standard:

DIN 787

Supplied with:

Complete, with extra-thick washer No. 375340 and tall nut No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

| | |
|---------------------|----------|
| Nut width e | 22 mm |
| narrow nut width a | 13.7 mm |
| Height k | 8 mm |
| Thread length b | 120 mm |
| T-slot nominal size | 14 mm |
| Thread G | M12 |
| Length L | 200 mm |
| Type | 787 |
| Type of product | Tee-bolt |

