

Mahr**Digital height gauge and marking-out system with data output, Marking height: 600mm****Order data**

Order number	445000 600
GTIN	4059192016814
Item class	43B

Description**Version:**

High contrast, 12 mm high LCD display. Stable ergonomic base with hardened and lapped surface for smooth movement without jolts. Beam and slide of hardened stainless steel. Large handwheel for positioning and measuring. Additional **fine adjustment and locking screw**.

Supplied with:

1 battery No. 081560 size CR2032, 1 carbide tipped scriber No. 445002.

Optional extras:

Holder for lever indicators No. 445004. Data cable No. 498940.

Technical description

Base width	98 mm
Weight	6.2 kg
Marking height	600 mm
Column cross section	35×15 mm
Base length	180 mm
Error limit	0.05 mm

Scale divisions	0.0005 in
Scale divisions	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	RS232C interface
Interface	Digimatic interface
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Services

Calibration Height gauge / height scriber maximum measuring range 1000 mm	024630 1000
---	-------------

Accessories

Connection cablesimplex with data key Type R2	498940 R2
Connection cable Type USB2	498938 USB2
Multi-receiver / USB keyboard interface Type	498975
Transmitter Type S4E	498966 S4E
Receiver / USB keyboard interface Type	498965
Connection cablesimplex with data key Type D2	498940 D2
Button cell / special battery Battery type CR2032	081560 CR2032
Spare scriber, carbide tipped	445002