



Digital depth gauge, Measuring range: 300mm



Order data

Order number	418802 300
GTIN	4045197528889
Item class	42A

Description

Version:

Easy-to-read display. Optimum sliding characteristics are ensured by **double Vee guides**. Measurement head of hard-coated aluminium with two tapped holes at 90° (M2.5) to take the measuring tips.

Supplied with:

Contact point No.434900 size2, 3measurement heads (150, 300 and 450 mm), 1battery No.081560 size LR44 and manufacturer's test certificate.

Optional extras:

All spare and special contact points No. 434900 - 434915 with M2.5 thread.

Technical description

Calibration	A1
Measuring range	0 - 300 mm
Cross-section measuring beam	23.5 × 9 mm
Reversible reading	0.0005 in
Reversible reading	0.01 mm
Error limit	0.04 mm
Article no of the battery / rechargeable battery fitted	081560 LR44
Number of batteries contained	1
Power supply	Battery-powered

Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Type of product	Depth gauge

Services

DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm	021010 300
Calibration Calipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Steel contact point Type 2	434900 2
Steel contact point Type 29/20	434900 29/20
Steel contact point Type 11/15	434900 11/15
Carbide contact point Type 18/1	434910 18/1
Steel contact point Type 10	434900 10
Steel contact point Type 28	434900 28
Carbide contact point Type 2	434910 2
Steel contact point Type 14	434900 14
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 14/40	434900 14/40
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 18/4	434900 18/4
Steel contact point Type 12	434900 12
Carbide contact point Type 10	434910 10
Steel contact point Type 14/20	434900 14/20

Steel contact point Type 11/35	434900 11/35
Steel contact point Type 29/10	434900 29/10
Carbide contact point Type 17	434910 17
Steel contact point Type 18/3	434900 18/3
Carbide contact point Type 11	434910 11
Carbide contact point Type 18/3	434910 18/3
Carbide contact point Type 14	434910 14
Steel contact point Type 24	434900 24
Ruby contact point Type 2	434915 2
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 20	434900 20
Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 13	434900 13
Button cell / special battery Battery type LR44	081560 LR44
Steel contact point Type 17	434900 17
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 11/20	434900 11/20
Steel contact point Type 14/15	434900 14/15
Steel contact point Type 18/1	434900 18/1
Steel contact point Type 39	434900 39
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 18/6	434900 18/6
Steel contact point Type 15	434900 15
Steel contact point Type 11	434900 11
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 16	434900 16
Carbide contact point Type 16	434910 16

Steel contact point Type 14/30

434900 14/30