



Digital depth gauge, Measuring range: 500mm



Order data

| | |
|--------------|---------------|
| Order number | 418802 500 |
| GTIN | 4045197528896 |
| Item class | 42A |

Description

Version:

Easy-to-read display. Optimum sliding characteristics are ensured by **double Vee guides**. Measurement head of hard-coated aluminium with two tapped holes at 90° (M2.5) to take the measuring tips.

Supplied with:

Contact point No.434900 size2, 3measurement heads (150, 300 and 450 mm), 1battery No.081560 size LR44 and manufacturer's test certificate.

Optional extras:

All spare and special contact points No. 434900 - 434915 with M2.5 thread.

Technical description

| | |
|---|-----------------|
| Cross-section measuring beam | 23.5 × 9 mm |
| Calibration | A1 |
| Measuring range | 0 - 500 mm |
| Reversible reading | 0.0005 in |
| Reversible reading | 0.01 mm |
| Error limit | 0.05 mm |
| Article no of the battery / rechargeable battery fitted | 081560 LR44 |
| Number of batteries contained | 1 |
| Power supply | Battery-powered |

| | |
|------------------------|---------------------------------|
| Standard | Manufacturer's standard |
| Reversible reading | mm / inch |
| Measurement technology | digital |
| Test certificate | Manufacturer's test certificate |
| Packaging | sturdy box |
| Type of product | Depth gauge |

Services

| | |
|--|------------|
| DAkkS calibration Calipers / depth gauges maximum measuring range 500 mm | 021010 500 |
| Calibration Calipers / depth gauges maximum measuring range 500 mm | 021000 500 |

Accessories

| | |
|---------------------------------|--------------|
| Steel contact point Type 13 | 434900 13 |
| Steel contact point Type 24 | 434900 24 |
| Steel contact point Type 18/5 | 434900 18/5 |
| Steel contact point Type 18/3 | 434900 18/3 |
| Carbide contact point Type 18/6 | 434910 18/6 |
| Carbide contact point Type 18/1 | 434910 18/1 |
| Steel contact point Type 11 | 434900 11 |
| Steel contact point Type 18/2 | 434900 18/2 |
| Steel contact point Type 28 | 434900 28 |
| Carbide contact point Type 16 | 434910 16 |
| Carbide contact point Type 10 | 434910 10 |
| Steel contact point Type 14 | 434900 14 |
| Steel contact point Type 11/30 | 434900 11/30 |
| Carbide contact point Type 18/5 | 434910 18/5 |
| Steel contact point Type 18/4 | 434900 18/4 |

| | |
|---|--------------|
| Ruby contact point Type 2 | 434915 2 |
| Carbide contact point Type 14 | 434910 14 |
| Carbide contact point Type 18/2 | 434910 18/2 |
| Steel contact point Type 29/10 | 434900 29/10 |
| Steel contact point Type 30/10 | 434900 30/10 |
| Steel contact point Type 17 | 434900 17 |
| Carbide contact point Type 18/3 | 434910 18/3 |
| Steel contact point Type 11/35 | 434900 11/35 |
| Steel contact point Type 14/40 | 434900 14/40 |
| Steel contact point Type 14/30 | 434900 14/30 |
| Steel contact point Type 15 | 434900 15 |
| Steel contact point Type 11/25 | 434900 11/25 |
| Steel contact point Type 18/6 | 434900 18/6 |
| Steel contact point Type 12 | 434900 12 |
| Carbide contact point Type 11 | 434910 11 |
| Steel contact point Type 14/15 | 434900 14/15 |
| Steel contact point Type 29/20 | 434900 29/20 |
| Carbide contact point Type 17 | 434910 17 |
| Steel contact point Type 10 | 434900 10 |
| Steel contact point Type 11/20 | 434900 11/20 |
| Carbide contact point Type 18/4 | 434910 18/4 |
| Steel contact point Type 2 | 434900 2 |
| Steel contact point Type 20 | 434900 20 |
| Steel contact point Type 16 | 434900 16 |
| Steel contact point Type 39 | 434900 39 |
| Button cell / special battery Battery type LR44 | 081560 LR44 |
| Steel contact point Type 18/1 | 434900 18/1 |
| Steel contact point Type 11/15 | 434900 11/15 |
| Carbide contact point Type 2 | 434910 2 |

Steel contact point Type 14/20

434900 14/20