



## Tee bolt (10.9. / 8.8.) complete, Type: 1614100



### Order data

|              |                |
|--------------|----------------|
| Order number | 375300 1614100 |
| GTIN         | 4020772080945  |
| Item class   | 35A            |

### Description

#### Version:

T-bolt, forged and rolled thread.

**Standard design**, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

#### Standard:

**DIN 787**

#### Supplied with:

**Complete**, with extra-thick washer No. 375340 and tall nut No. 375385.

#### Note:

- **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

|                     |          |
|---------------------|----------|
| Nut width e         | 25 mm    |
| Height k            | 9 mm     |
| narrow nut width a  | 15.7 mm  |
| Thread length b     | 65 mm    |
| T-slot nominal size | 16 mm    |
| Thread G            | M14      |
| Length L            | 100 mm   |
| Type                | 787      |
| Type of product     | Tee-bolt |

