



## Tee bolt (10.9. / 8.8.) complete, Type: 1212160



### Order data

Order number	375300 1212160
GTIN	4020772081508
Item class	35A

### Description

#### Version:

T-bolt, forged and rolled thread.

**Standard design**, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

#### Standard:

**DIN 787**

#### Supplied with:

**Complete**, with extra-thick washer No. 375340 and tall nut No. 375385.

#### Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

Thread length b	100 mm
Nut width e	18 mm
Height k	7 mm
T-slot nominal size	12 mm
narrow nut width a	11.7 mm
Thread G	M12
Length L	160 mm
Type	787
Type of product	Tee-bolt

