



Tee bolt (10.9. / 8.8.) single, Type: 8850



Order data

| | |
|--------------|---------------|
| Order number | 375305 8850 |
| GTIN | 4020772080372 |
| Item class | 35A |

Description

Version:

T-bolt, forged and rolled thread.

Standard design, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

| | |
|---------------------|----------|
| T-slot nominal size | 8 mm |
| Nut width e | 13 mm |
| Thread length b | 35 mm |
| narrow nut width a | 7.7 mm |
| Height k | 6 mm |
| Thread G | M8 |
| Length L | 50 mm |
| Type | 787 |
| Type of product | Tee-bolt |

