



Tee bolt (10.9. / 8.8.) single, Type: 1212160



Order data

Order number	375305 1212160
GTIN	4020772081492
Item class	35A

Description

Version:

T-bolt, forged and rolled thread.

Standard design, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

T-slot nominal size	12 mm
Thread length b	100 mm
Nut width e	18 mm
Height k	7 mm
narrow nut width a	11.7 mm
Thread G	M12
Length L	160 mm
Type	787
Type of product	Tee-bolt

