

Mitutoyo**Digital height gauge and marking-out system with data output, Marking height: 300mm****Order data**

Order number	445135 300
GTIN	6923903400118
Item class	44A

Description**Version:**

Large, high contrast LCD display for easy, error-free reading (character height 10 mm). Rapid and precise adjustment using exact handwheel control. Robust, stable version with solid base and ergonomically shaped handle for effortless handling. Zero / ABS for zeroing in any position (e.g. comparative measurement) or return to absolute scale.

Supplied with:

1 battery No. 081560 size 357, 1 carbide tipped scriber No. 443510 size 300 (suitable for both sizes).

Optional extras:

Holder No. 445180, data cable No. 497080.

Calibration: E1

Scale divisions: 0.01 mm

Error limit: 0.03 mm

Column cross section: 35×15 mm

Battery life approx.: 2000 h

Base length: 160 mm

Base width: 122 mm

Technical description

Base length	160 mm
Column cross section	35×15 mm
Base width	122 mm
Weight	4.6 kg
Marking height	300 mm
Error limit	0.03 mm
Scale divisions	0.01 mm
Battery life approx.	2000 h
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Services

Calibration Height gauge / height scriber maximum measuring range 300 mm	014350 300
Labelling laser-etched Type	018940
Calibration Height gauge / height scriber maximum measuring range 300 mm	024630 300
DAkkS recalibration, vernier height gauge 300	024640 300

Accessories

Button cell / special battery Battery type 357	081560 357
Universal square holding arm	445180
Connecting cable with data switch Type D2	497100 D2
Connecting cable Type USB2	497080 USB2
Connecting cable Type D2	497080 D2
Multi-receiver / USB keyboard interface Type	498975
Receiver / USB keyboard interface Type	498965
Transmitter Type S1	498966 S1
Connecting cable with data switch Type USB2	497100 USB2
Connecting cable Type D1	497080 D1
Connecting cable with data switch Type D1	497100 D1
Spare scriber, carbide tipped for marking heights 300 mm	443510 300