



Digital depth gauge, Measuring range: 800mm



Order data

Order number	418802 800
GTIN	4045197529107
Item class	42A

Description

Version:

Easy-to-read display. Optimum sliding characteristics are ensured by **double Vee guides**. Measurement head of hard-coated aluminium with two tapped holes at 90° (M2.5) to take the measuring tips.

Supplied with:

Contact point No.434900 size2, 3measurement heads (150, 300 and 450 mm), 1battery No.081560 size LR44 and manufacturer's test certificate.

Optional extras:

All spare and special contact points No. 434900 - 434915 with M2.5 thread.

Technical description

Measuring range	0 - 800 mm
Calibration	A1
Cross-section measuring beam	23.5 × 9 mm
Reversible reading	0.0005 in
Reversible reading	0.01 mm
Error limit	0.06 mm
Article no of the battery / rechargeable battery fitted	081560 LR44
Number of batteries contained	1
Power supply	Battery-powered

Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Type of product	Depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000

Accessories

Steel contact point Type 29/10	434900 29/10
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 17	434900 17
Carbide contact point Type 18/1	434910 18/1
Steel contact point Type 14/15	434900 14/15
Steel contact point Type 18/2	434900 18/2
Carbide contact point Type 17	434910 17
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 2	434900 2
Steel contact point Type 14	434900 14
Steel contact point Type 14/20	434900 14/20
Steel contact point Type 16	434900 16
Steel contact point Type 20	434900 20
Carbide contact point Type 18/2	434910 18/2
Steel contact point Type 11/20	434900 11/20

Carbide contact point Type 18/4	434910 18/4
Steel contact point Type 13	434900 13
Steel contact point Type 11	434900 11
Carbide contact point Type 18/3	434910 18/3
Steel contact point Type 28	434900 28
Steel contact point Type 24	434900 24
Carbide contact point Type 10	434910 10
Carbide contact point Type 11	434910 11
Steel contact point Type 39	434900 39
Steel contact point Type 14/30	434900 14/30
Ruby contact point Type 2	434915 2
Steel contact point Type 18/1	434900 18/1
Carbide contact point Type 18/6	434910 18/6
Steel contact point Type 11/30	434900 11/30
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 18/3	434900 18/3
Steel contact point Type 11/25	434900 11/25
Carbide contact point Type 16	434910 16
Steel contact point Type 10	434900 10
Steel contact point Type 18/6	434900 18/6
Carbide contact point Type 14	434910 14
Carbide contact point Type 18/5	434910 18/5
Steel contact point Type 15	434900 15
Steel contact point Type 11/15	434900 11/15
Button cell / special battery Battery type LR44	081560 LR44
Carbide contact point Type 2	434910 2
Steel contact point Type 12	434900 12
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 18/4	434900 18/4

Steel contact point Type 29/20

434900 29/20