



Vernier height gauge with magnifying glass, Marking height: 600mm



Order data

Order number	443805 600
GTIN	4045197326843
Item class	42D

Description

Version:

Strong base with lapped standing surface. Reading 0.02 mm with fine adjustment. The scribe is **carbide tipped**. With adjustable measuring beam, magnifying glass and locking screw.

Technical description

Base length	175 mm
Column cross section	35×12 mm
Base width	120 mm
Calibration	E1
Marking height	600 mm
Vernier	1/50 mm
Error limit	0.06 mm
Standard	Manufacturer's standard

Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum measuring range 1000 mm	024630 1000
DAkkS calibrationHeight gauge / height scriber maximum measuring range 1000 mm	024640 1000

Accessories

Spare scriber, carbide tipped Type E	443816 E
Spare scriber, carbide tipped Type R	443816 R