



Digital height gauge and marking-out system, Marking height: 300mm



Order data

Order number	443850 300
GTIN	4045197204745
Item class	42D

Description

Version:

Digital height gauge and marking out system with fine adjustment. Sturdy stand with ground base.

Easily legible LCD display. Scriber carbide tipped.

Function:

Zeroing possible in any position.

Hold function (HOLD).

ABS / INC / TOL and SET.

Supplied with:

1 battery No. 081560 size 357, 1 carbide tipped scriber No. 443851.

Technical description

Base width	90 mm
Base length	135 mm
Marking height	300 mm
Weight	2.1 kg

Column cross section	23×6.1 mm
Error limit	0.05 mm
Scale divisions	0.0005 in
Scale divisions	0.01 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum measuring range 300 mm	024630 300
DAkkS calibrationHeight gauge / height scriber maximum measuring range 300 mm	024640 300

Accessories

Spare scriber, carbide tipped for marking heights 300 mm	443851 300
Spare scriber, carbide tipped for marking heights 600 mm	443851 600
Button cell / special battery Battery type 357	081560 357