



## Tee bolt (10.9. / 8.8.) single, Type: 141280



### Order data

Order number	375305 141280
GTIN	4020772080464
Item class	35A

### Description

#### Version:

T-bolt, forged and rolled thread.

**Standard design**, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

#### Standard:

##### DIN 787

#### Supplied with:

**Single**, without nut and washer.

#### Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

#### Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

T-slot nominal size	14 mm
Height k	8 mm
Thread length b	55 mm
narrow nut width a	13.7 mm
Nut width e	22 mm
Thread G	M12
Length L	80 mm
Type	787
Type of product	Tee-bolt

