



Tee bolt (10.9. / 8.8.) complete, Type: 141280



Order data

Order number	375300 141280
GTIN	4020772080907
Item class	35A

Description

Version:

T-bolt, forged and rolled thread.

Standard design, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

Standard:

DIN 787

Supplied with:

Complete, with extra-thick washer No. 375340 and tall nut No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

T-slot nominal size	14 mm
Thread length b	55 mm
narrow nut width a	13.7 mm
Height k	8 mm
Nut width e	22 mm
Thread G	M12
Length L	80 mm
Type	787
Type of product	Tee-bolt

