



## Tee bolt (10.9. / 8.8.) complete, Type: 202080



### Order data

Order number	375300 202080
GTIN	4020772084301
Item class	35A

### Description

#### Version:

T-bolt, forged and rolled thread.

**Standard design**, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

#### Standard:

**DIN 787**

#### Supplied with:

**Complete**, with extra-thick washer No. 375340 and tall nut No. 375385.

#### Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

T-slot nominal size	20 mm
Nut width e	32 mm
narrow nut width a	19.7 mm
Height k	12 mm
Thread length b	55 mm
Thread G	M20
Length L	80 mm
Type	787
Type of product	Tee-bolt

