

Mitutoyo
External micrometer, Measuring range: 200-225mm

Order data

Order number	420500 200-225
GTIN	4946368215013
Item class	44A

Description
Version:
Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

From size 100-125, enamelled cast frame.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Barrel Ø	18 mm
Micrometer barrel graduations	1/50 mm
Spindle pitch	1/50 mm
Measuring range	200 - 225 mm
Scale divisions	0.01 mm
Spindle Ø	6.35 mm
Type of measurement face	Carbide tipped
Calibration	B2

Error limit	4 μm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 500 mm	022050 500
Calibration External micrometer including setting dimension maximum measuring range 300 mm	022040 300