

Garant**External micrometer, Measuring range: 0-25mm****Order data**

Order number	420402 0-25
GTIN	4045197367327
Item class	41B

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for single-handed operation and stand operation.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Scale divisions	0.01 mm
Micrometer barrel graduations	1/50 mm
Measuring range	0 - 25 mm
Spindle Ø	6.5 mm
Barrel Ø	19 mm
Calibration	B1
Standard	ISO 3611
Measurement deviation E MPE	±2 µm

Ratchet	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/420402-0-25>