

**Mitutoyo**
**External micrometer, Measuring range: 275-300mm**

**Order data**

Order number	420500 275-300
GTIN	4946368215044
Item class	44A

**Description**
**Version:**
**Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

From size 100-125, enamelled cast frame.

**Supplied with:**

From size 25-50 including 1 setting standard.

**Technical description**

Measuring range	275 - 300 mm
Spindle Ø	6.35 mm
Type of measurement face	Carbide tipped
Spindle pitch	1/50 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Barrel Ø	18 mm
Calibration	B2

Error limit	5 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 500 mm	022050 500
Calibration External micrometer including setting dimension maximum measuring range 300 mm	022040 300