

Mitutoyo**External micrometer, Measuring range: 0-25mm****Order data**

Order number	420500 0-25
GTIN	4946368385624
Item class	44A

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

From size 100-125, enamelled cast frame.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	0 - 25 mm
Micrometer barrel graduations	1/50 mm
Barrel Ø	18 mm
Spindle pitch	1/50 mm
Spindle Ø	6.35 mm
Type of measurement face	carbide tipped
Scale divisions	0.01 mm
Calibration	B1

Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100