Garant

External micrometer, Measuring range: 25-50mm

Order data

Order number	420402 25-50
GTIN	4045197367334
Item class	41B

Description

Version:
Precision lapped, carbide-tipped measuring faces.
Hardened and ground measuring spindle. Locking by clamping lever.
With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.
With clearly engraved, black divisions and numerals.
With combined sensitive ratchet for one-hand operation and operation within the bracket.
Supplied with:
From size 25-50 including 1 setting standard.

Technical description

Measuring range	25 - 50 mm
Spindle ∅	6.5 mm
Scale divisions	0.01 mm
Number of micrometer standards	1
Micrometer barrel graduations	1/50 mm
Barrel ∅	19 mm
Calibration	B2
Standard	DIN 863

Ratchet	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

CalibrationExternal micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibrationExternal micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Micrometer setting standard overall length 25 mm	421100 25