

3D edge finder with indicator light long, Tool shank Ø: 20mm



Order data

Order number	359078 20
GTIN	4260192270520
Item class	38D

Description

Version:

The spring-mounted spherical tip protects the unit from damage if contact is too violent.
Functional parts hardened and ground.
Contact accuracy ± 0.005 mm.

Function:

When **the spherical tip contacts a metallic component**, batteries cause the lamp to light =
Detection of the reference point.

Application:

- **Alignment of component reference surfaces or edges.**
- **Determination of bore centres to the machine spindle.**

When making contact in the Z axis, the reference length has to be determined using the pre-setter and taken into account.

Supplied with:

Supplied with special battery No. 081560 A23.
Spherical point Ø: 10 mm
Overall length: 167 mm

Technical description

Overall length	167 mm
Tool shank Ø	20 mm
Spherical point Ø	10 mm
Article no of the battery / rechargeable battery fitted	081560 A23
Number of batteries contained	1
Power supply	Battery-powered
Type of product	Probes

Accessories

Button cell / special battery Battery type A23	081560 A23
--	------------