

**Mitutoyo**
**External micrometer, Measuring range: 25-50mm**

**Order data**

Order number	420500 25-50
GTIN	4946368385631
Item class	44A

**Description**
**Version:**
**Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

From size 100-125, enamelled cast frame.

**Supplied with:**

From size 25-50 including 1 setting standard.

**Technical description**

Type of measurement face	carbide tipped
Spindle Ø	6.35 mm
Scale divisions	0.01 mm
Micrometer barrel graduations	1/50 mm
Measuring range	25 - 50 mm
Spindle pitch	1/50 mm
Barrel Ø	18 mm
Calibration	B2

Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

## Accessories

Micrometer setting standard overall length 25 mm	421100 25
--	-----------