

 Mahr**External micrometer, Measuring range: 25-50mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 420410 25-50  |
| GTIN         | 4059192003654 |
| Item class   | 43A           |

**Description****Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

**Supplied with:**

From size 25-50 including 1 setting standard.

**Technical description**

|                               |            |
|-------------------------------|------------|
| Scale divisions               | 0.01 mm    |
| Measuring range               | 25 - 50 mm |
| Micrometer barrel graduations | 1/50 mm    |
| Barrel Ø                      | 17.5 mm    |
| Spindle Ø                     | 6.5 mm     |
| Calibration                   | B2         |
| Error limit                   | 4 µm       |
| Standard                      | DIN 863    |
| Measurement technology        | analogue   |

|                 |                          |
|-----------------|--------------------------|
| Packaging       | sturdy box               |
| Type of product | External tube micrometer |

### Services

|  |            |
|--|------------|
| DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm | 022050 100 |
| Calibration External micrometer including setting dimension maximum measuring range 100 mm       | 022040 100 |

### Accessories

|  |           |
|--|-----------|
| Micrometer setting standard overall length 25 mm | 421100 25 |
|--|-----------|