

Mitutoyo
External micrometer, Measuring range: 0-25mm

Order data

Order number	420540 0-25
GTIN	4946368508535
Item class	44A

Description
Version:
Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Type of measurement face	Carbide tipped
Barrel Ø	18 mm
Spindle Ø	6.35 mm
Scale divisions	0.01 mm
Micrometer barrel graduations	1/50 mm
Measuring range	0 - 25 mm
Weight	0.3 kg
Calibration	B1
Error limit	2 µm

Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100