

## Edge finder, Contact point Ø: 10mm



### Order data

Order number	359000 10
GTIN	4045197350237
Item class	38D

### Description

**Version:**

The contact point has a flexible connection to the body via a spring, with an **alignment accuracy of 0.01 mm.**

All parts fully hardened and ground.

**Version of the advertising text:**

**Alignment accuracy 0.01 mm.**

**Application:**

For alignment of component reference surfaces or edges.

Spindle speed approx. 600 rpm.

**Use of the advertising text:**

For alignment of component reference surfaces or edges. Spindle speed approx. 600 rpm.

### Technical description

Overall length	84 mm
Tool shank Ø	10 mm
Contact point Ø	10 mm
Type of product	Probes

---

## Accessories

Spare spring for edge finder Ø×Overall length 4,6X40 mm	359010 4,6X40
Spare spring for edge finder Ø×Overall length 2,6X25 mm	359010 2,6X25